

**SOLID ABS 1919 13 G-2FSH**



Sample photo

<b>Order symbol:</b>	ABS 1919 13 G-2FSH	<b>EAN:</b>	6418074053428
<b>Product nbr:</b>	9880401	<b>EI. number:</b>	
<b>Description:</b>	Enclosure, ABS	<b>Finland:</b>	3435770
<b>Remarks:</b>	Grey hinged cover	<b>Electric No. Sweden:</b>	9880401

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
<b>mm:</b>	188	188	130	EKHXT                      Mounting plate isolated
<b>inch:</b>	7.4	7.4	5.1	EKV 12                      DIN-35 Mounting rail

Materials:	Rating:
<b>Material:</b> ABS	Ingress Protection (EN 60529): IP65
<b>Base colour:</b> RAL 7035 -light grey	Impact Resistance (EN 62262): IK08
<b>Cover screws material:</b> Polyamide	Electrical insulation: Totally insulated
<b>Cover colour:</b> RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
<b>Cover screws colour:</b> Grey	Flammability Rating: UL 94 HB
<b>Gasket material:</b> Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650
	NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:	Certificates:
<b>Temperature °C (short term):</b> -40 ... 80 °C	Gost R
<b>Temperature °C (continuous):</b> -40 ... 60 °C	
<b>Temperature °F (short term):</b> -40 ... 175 °F	
<b>Temperature °F (continuous):</b> -40 ... 140 °F	

Accessories:
EKHVT                      Mounting plate

