



Sample photo

**Order symbol:** PCT 050705  
**Product nbr:** 7022521  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074003720  
**EI. number:**  
 Finland: 3423524  
 Electric No. Denmark: 8212002539  
 Electric No. Italy: 7302010  
 Electric No. Sweden: 7022521

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:			Accessories:		
	Length	Width	Height		
mm:	65	50	45	TM 0507	Mounting plate
inch:	2.6	2.0	1.8	TRM 0507	DIN-15 Mounting rail
<b>Materials:</b>			TF 28037	Wall fastening lug (4 pcs)	
<b>Material:</b>	Polycarbonate		TH A	Grey plastic hinges (2 pcs)	
<b>Base colour:</b>	RAL 7035 -light grey		<b>Rating:</b>		
<b>Cover screws material:</b>	Stainless steel		Ingress Protection (EN 60529): IP66/67		
<b>Cover colour:</b>	Clear transparent		Impact Resistance (EN 62262): IK07/IK08		
<b>Gasket material:</b>	Polyurethane		Electrical insulation: Totally insulated		
<b>Temperatures:</b>			Halogen free (DIN/VDE 0472, Part 815): 1		
<b>Temperature °C (short term):</b>	-40 ... 120 °C		UV resistance: UL 508		
<b>Temperature °C (continuous):</b>	-40 ... 80 °C		Flammability Rating: UL 746C 5V		
<b>Temperature °F (short term):</b>	-40 ... 250 °F		Glow Wire Test (IEC 695-2-1) °C: 960		
<b>Temperature °F (continuous):</b>	-40 ... 175 °F		NEMA Class: NEMA 1, 4, 4X, 12, 13		
<b>Accessories:</b>			<b>Certificates:</b>		
TM 0505	Mounting plate		SGS Fimko		
			Gost R		

