



Sample photo

Order symbol: PCT 050705
Product nbr: 7022521
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074003720
EI. number:
 Finland: 3423524
 Electric No. Denmark: 8212002539
 Electric No. Italy: 7302010
 Electric No. Sweden: 7022521

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Accessories:	
mm:		65	50	45	TM 0507	Mounting plate
inch:		2.6	2.0	1.8	TRM 0507	DIN-15 Mounting rail
Materials:					TF 28037	Wall fastening lug (4 pcs)
Material:	Polycarbonate				TH A	Grey plastic hinges (2 pcs)
Base colour:	RAL 7035 -light grey				Rating:	
Cover screws material:	Stainless steel				Ingress Protection (EN 60529): IP66/67	
Cover colour:	Clear transparent				Impact Resistance (EN 62262): IK07/IK08	
Gasket material:	Polyurethane				Electrical insulation: Totally insulated	
Temperatures:					Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °C (short term):	-40 ... 120 °C				UV resistance: UL 508	
Temperature °C (continuous):	-40 ... 80 °C				Flammability Rating: UL 746C 5V	
Temperature °F (short term):	-40 ... 250 °F				Glow Wire Test (IEC 695-2-1) °C: 960	
Temperature °F (continuous):	-40 ... 175 °F				NEMA Class: NEMA 1, 4, 4X, 12, 13	
Accessories:					Certificates:	
TM 0505	Mounting plate				SGS Fimko	
					Gost R	

