

MNX ABS 100/125 HG



Sample photo

Order symbol: ABS 100/125 HG
Product nbr: 6081304
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074022820
EI. number:
 Finland: 3420515
 Electric No. Denmark: 8212023152
 Electric No. Italy: 7361035
 Electric No. Sweden: 2535718

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	130	80	125	MIN 5	DIN-15 Mounting rail
inch:	5.1	3.1	4.9	MIN 10	DIN-15 Mounting rail
				MIV 5	DIN-35 Mounting rail
				MIV 10	DIN-35 Mounting rail
				FP A 100/130	Front plate (Aluminium)
				HFP 130	Front plate hinge series
				FP 22046	Wall fastening lug (4 pcs)
Materials:				Rating:	
Material:	ABS			Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07	
Cover screws material:	Polyamide			Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey			Flammability Rating: UL 94 HB	
Gasket material:	TPE			Glow Wire Test (IEC 695-2-1) °C: 650	
				NEMA Class: NEMA 1, 4, 4X, 6	
Temperatures:				Certificates:	
Temperature °C (short term):	-40 ... 80 °C			SGS Fimko	
Temperature °C (continuous):	-40 ... 60 °C			Gost R	
Temperature °F (short term):	-40 ... 175 °F				
Temperature °F (continuous):	-40 ... 140 °F				
Accessories:					
MIV 100	Mounting plate (Galvanized steel)				

