

**SOLID ABS 2828 13 G**



Sample photo

**Order symbol:** ABS 2828 13 G  
**Product nbr:** 5880362  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074039064  
**EI. number:**  
 Finland: 3423763  
 Electric No. Italy: 7410140  
 Electric No. Sweden: 2539717

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	278	278	130	EKOXT	Mounting plate isolated
inch:	10.9	10.9	5.1	EKV 22	DIN-35 Mounting rail
				EKOZR	Extension frame

Materials:	
<b>Material:</b>	ABS
<b>Base colour:</b>	RAL 7035 -light grey
<b>Cover screws material:</b>	Polyamide
<b>Cover colour:</b>	RAL 7035 -light grey
<b>Cover screws colour:</b>	Grey
<b>Gasket material:</b>	Polyurethane

Rating:
Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
Flammability Rating: UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:	
<b>Temperature °C (short term):</b>	-40 ... 80 °C
<b>Temperature °C (continuous):</b>	-40 ... 60 °C
<b>Temperature °F (short term):</b>	-40 ... 175 °F
<b>Temperature °F (continuous):</b>	-40 ... 140 °F

Certificates:
SGS Fimko

Accessories:	
EKOVT	Mounting plate

