



Sample photo

Order symbol: AR664CHSS
Product nbr: 8561041
Description: PC Enclosure
Remarks: Hinged opaque cover w/S.S.
 Quick release latch

EAN: 6418074066978
EI. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:	
mm:	152	152	102	ABP66	Painted Steel Back Panel
inch:	6.0	6.0	4.0	ALBP66	Aluminum Back Panel
Materials:				ADFP66	Dead Front Panel w/ screws
Material:	Polycarbonate			ASP66	Aluminum Swing Panel
Base colour:	RAL 7035 -light grey			ASPK66	Swing Panel Kit incl. Panel
Cover screws material:	Stainless steel			ASPHK6	Swing Panel Kit w/o Panel
Cover colour:	RAL 7035 -light grey			AMFL6	6" Mounting Flange Set
Gasket material:	Polyurethane			Rating:	
Temperatures:				Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (short term):	-40 ... 140 °C			Impact Resistance (EN 62262): IK09	
Temperature °C (continuous):	-40 ... 80 °C			Electrical insulation: Totally insulated	
Temperature °F (short term):	-40 ... 284 °F			Halogen free (DIN/VDE 0472, Part 815): 0	
Temperature °F (continuous):	-40 ... 175 °F			UV resistance: UL 508	
Accessories:				Flammability Rating: UL 508	
APBP66	PVC Back Panel			Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13	

