

Order symbol: AR181610CHSS
Product nbr: 8561071
Description: PC Enclosure
Remarks: Hinged opaque cover w/S.S.
 Quick release latch

EAN: 6418074067227
EI. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:
mm:	457	406	254	ALBP1816 Aluminum Back Panel
inch:	18.0	16.0	10.0	ADFP1816 Dead Front Panel w/ screws
Materials:				ASP1816 Aluminum Swing Panel
Material:	Polycarbonate			APSPK1816 Plastic Swing Panel Kit incl. Panel
Base colour:	RAL 7035 -light grey			ASPK1816 Swing Panel Kit incl. Panel
Cover screws material:	Stainless steel			AMFL16 16" Mounting Flange Set
Cover colour:	RAL 7035 -light grey			Rating:
Gasket material:	Polyurethane			Ingress Protection (EN 60529): IP66/IP67
Temperatures:				Impact Resistance (EN 62262): IK09
Temperature °C (short term):	-40 ... 140 °C			Electrical insulation: Totally insulated
Temperature °C (continuous):	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 0
Temperature °F (short term):	-40 ... 284 °F			UV resistance: UL 508
Temperature °F (continuous):	-40 ... 175 °F			Flammability Rating: UL 508
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960
ABP1816	Painted Steel Back Panel			NEMA Class: NEMA 4, 4X, 12 and 13

