

FIBOX	Supplier scorecard yyyy					
	Supplier name: nn	Rating (max 5):	0,00	0,00 %		
	Date: dd.mm.yyyy					
	Positive findings	Areas to improve			Passed: 80 % of max	
					Require development: 50-80 %	
					Failed: <50 %	
Area	Scorecard criteria	Score	Comments	Area Weight	Area Rating	Weighted rating
Financial rating	Rating alfa or other applicable			10 %	0,00	0,00
Quality	DPPM (1000)			20 %	0,00	0,00
	ISO9001					
	ISO14001					
	ISO45001					
Health & Safety	LTIFR monitoring (sick leave >1 day), prevention			15 %	0,00	0,00
Delivery	Delivery term (DAP)			20 %	0,00	0,00
	Order confirmations on time					
	Delayed customer deliveries handling					
	OTD-C +3 days (97%)					
Cost & Cash	Payment term (90 days)			20 %	0,00	0,00
	Purchase price development (decrease)					
	Bonus agreement (at place)					
Business development	Contracting (NDA, CoC, Fibox T&Cs)			10 %	0,00	0,00
	Sustainability / ESG					
	Continuous improvement program					
Customer service	Technical capabilities and skills			5 %	0,00	0,00
	Responsiveness					
	Easiness to operate					