

ARCA IEC WITH TRANSPARENT DOOR

DESIGNED FOR APPLICATIONS IN

- WATER AND WASTEWATER
- ENERGY TRANSITION
- FACTORY AUTOMATION



IP 66

-40 °C

+80 °C



ARCA IEC TRANSPARENT DOORS

TRANSPARENT COVERS MADE OF POLYCARBONATE

BENEFITS OF ARCA TRANSPARENT DOORS

- High density class IP66 (S=IP65)
- High impact resistance IK09
- Greater visibility
- Excellent chemical and corrosion resistance
- Lightweight yet robust construction
- UV-stabilized material
- Wide temperature operating range
- Low maintenance with long service life

BENEFITS OF ARCA IEC-RANGE

- UV-Resistant (UL 508)
- Double Insulated (1500VDC)
- Self-Extinguishing
- Corrosion Free
- High impact resistance
- Excellent ingress protection (up to IP66/IP67)
- Easy installation
- Wide operating temperature range
- Maintenance free
- Halogen free



See More. React Faster. Protect Better.

Introducing the new **Fibox ARCA T** with a transparent door - engineered to give you instant visibility into your cabinet without ever opening it.

Monitor critical components at a glance, streamline maintenance, and enhance safety with a clean, modern design that fits seamlessly into any environment.

With greater clarity and complete control, ARCA T helps you work smarter, faster, and more confidently.

Transparency that drives efficiency - right where you need it.



Dimensions (H x W x D)	Description (Locking)	With mounting plate		Without mounting plate	
		Fibox code	Symbol	Fibox code	Symbol
200 x 300 x 150 mm	Complete with DB3 lock and transparent door	8121020	ARCA 203015T	8121020N	ARCA 203015T No MP
300 x 200 x 150 mm	Complete with DB3 lock and transparent door	8121002	ARCA 302015T	8121002N	ARCA 302015T No MP
300 x 300 x 210 mm	Complete with DB3 lock and transparent door	8121005	ARCA 303021T	8121005N	ARCA 303021T No MP
300 x 400 x 150 mm	Complete with DB3 lock and transparent door	8121022	ARCA 304015T	8121022N	ARCA 304015T No MP
300 x 400 x 210 mm	Complete with DB3 lock and transparent door	8121023	ARCA 304021T	8121023N	ARCA 304021T No MP
400 x 300 x 150 mm	Complete with DB3 lock and transparent door	8121006	ARCA 403015T	8121006N	ARCA 403015T No MP
400 x 300 x 210 mm	Complete with DB3 lock and transparent door	8121007	ARCA 403021T	8121007N	ARCA 403021T No MP
400 x 400 x 210 mm	Complete with DB3 lock and transparent door	8121009	ARCA 404021T	8121009N	ARCA 404021T No MP
400 x 500 x 210 mm	Complete with DB3 lock and transparent door	8121025	ARCA 405021T	8121025N	ARCA 405021T No MP
400 x 600 x 210 mm	Complete with DB3 lock and transparent door	8121026	ARCA 406021T	8121026N	ARCA 406021T No MP
500 x 400 x 210 mm	Complete with DB3 lock and transparent door	8121011	ARCA 504021T	8121011N	ARCA 504021T No MP
500 x 500 x 210 mm	Complete with DB3 lock and transparent door	8121032	ARCA 505021T	8121032N	ARCA 505021T No MP
600 x 400 x 210 mm	Complete with DB3 lock and transparent door	8121012	ARCA 604021T	8121012N	ARCA 604021T No MP
400 x 300 x 150 mm	Complete with swinghandle and transparent door	8121086	ARCA 403015ST	8121086N	ARCA 403015ST No MP
400 x 300 x 210 mm	Complete with swinghandle and transparent door	8121087	ARCA 403021ST	8121087N	ARCA 403021ST No MP
400 x 400 x 210 mm	Complete with swinghandle and transparent door	8121089	ARCA 404021ST	8121089N	ARCA 404021ST No MP
400 x 500 x 210 mm	Complete with swinghandle and transparent door	8121105	ARCA 405021ST	8121105N	ARCA 405021ST No MP
400 x 600 x 210 mm	Complete with swinghandle and transparent door	8121106	ARCA 406021ST	8121106N	ARCA 406021ST No MP
500 x 400 x 210 mm	Complete with swinghandle and transparent door	8121091	ARCA 504021ST	8121091N	ARCA 504021ST No MP
500 x 500 x 210 mm	Complete with swinghandle and transparent door	8121112	ARCA 505021ST	8121112N	ARCA 505021ST No MP
600 x 400 x 210 mm	Complete with swinghandle and transparent door	8121092	ARCA 604021ST	8121092N	ARCA 604021ST No MP





Fibox Group

Keilaranta 17

02150 Espoo, Finland

Tel.: +358 207 785 700

E-mail: sales@fibox.com

www.fibox.com

ALL ARCA SOLUTIONS HERE

