

CERTIFICATE FI/40848

Our Ref. HEL-CERT190900589-03

Product Range of enclosures

Type CAB PCQ ... (QUICK)

Trademark FIBOX

Certificate Holder Fibox Oy Ab

HTC Center Keilaranta 19

FI-02150, Espoo, Finland

Technical information Degree of protection (EN 60529)

Mechanical strength (EN 62262) Mechanical strength (EN 61439-4)

Static loads

IP66 / IP67 IK08 +35/-25°C 6 J +35/-25°C

mounting plate 1 kg/dm² swing door /hinges 2 kg

mounting rail 10 kg/rail max. 30 kg/box

Other information Material: Polycarbonate

Empty enclosure

The serie includes the following types, see page 2 of this Certificate

The product is certified according to the following

standard(s)

EN 62208:2011

EN 61439-3:2012 (applicable parts) EN 61439-4:2013 (applicable parts)

Validity This certificate is valid until 23 October 2025 provided that the Conditions for FI

certification are met. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is

brought onto market and that the conditions for FI certification are met.

Date of issue 23 October 2020

SGS Fimko Ltd

Signature

Sixten Lökfors

Project Manager

Page 1 of 2

This document is issued by the Company under its Germany under its Germ

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and iurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland t. +358 9 696 361 www.sgs.fi

Business ID 0978538-5

Member of the SGS Group (SGS SA)



Page 2 of 2 to Certificate: FI/40848

Manufacturer Fibox Oy Ab

HTC Center

Keilaranta 19, FI-02150, Espoo, Finland

Manufacturing site FiboxPAM Ov

Rajasilta 6, FI-33880, Lempäälä, Finland

Directive information The certified product(s) fulfils requirements of mentioned standard(s) which are

harmonised under the Low Voltage Directive (2014/35/EU)

at the date of issue of the certificate.

Additional information This certificate replaces certificate FI 40375 dated 05 September 2019, due to new

testing.

The series includes the

following types

Size (mm)	IP-code	IK-code
200x300x170	IP66 / IP67	IK08
300x300x170	IP66 / IP67	IK08
400x300x170	IP66 / IP67	IK08
400x300x230	IP66 / IP67	IK08
400x400x170	IP66 / IP67	IK08
600x300x170	IP66 / IP67	IK08
600x400x210	IP66 / IP67	IK08
600x400x270	IP66 / IP67	IK08
	200x300x170 300x300x170 400x300x170 400x300x230 400x400x170 600x300x170 600x400x210	200x300x170

QUICK is catalogue code for CAB... types

Accessories

IP-code IK-code Type

Mounting plate **EKIV 23...EKIV64**

Extension frame **IP65 IK08 EKI EXT 44**

Cover screw heads CS 12137, SS 12136,

HS 12112 ja BS 12138

Corner sleeve plug SP 12087 Wall fastening lug FP 12017

Swing door kit MB 12225

Swing door/front plates FP 12-23...FP 18x3-64 IP20X FP A 64 IP20X

Front plates FP A 23 Mounting rail frame DRF 23...DRF 63/64

Mounting rail EKIV 17, -27, -37

Inspection windows EKI L43/40G + L43 II **IP65 IK08** Inspection windows EKI L44/40G + L44 II IP55 IK08

Based on 252268-1, 277543-1, 297570-1



Page 2 of 2

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_condition Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland t. +358 9 696 361 www.sgs.fi