

MANUFACTURERS DECLARATION

This declaration is to certify that the enclosure product line described below, conform to the following product characteristics.

Fibox TEMPO PC

Technical information

<i>Material</i>	<i>Polycarbonate, gasket PUR or TPE</i>
<i>Colour base</i>	<i>RAL 7035</i>
<i>Colour cover</i>	<i>RAL 7035 or clear transparent</i>
<i>Ingress Protection (EN 60529)</i>	<i>IP65</i>
<i>Impact Resistance (EN 62262)</i>	<i>IK08 +35°C/-25°C front IK07 +35°C/-25°C sides</i>
<i>Max operating temp range long term</i>	<i>-40°C. . . +80°C</i>
<i>Material Flammability Rating</i>	<i>UL 94-5VA, UL 94-V0</i>
<i>Glow wire test</i>	<i>960°C</i>
<i>Static loads</i>	<i>Mounting plate 1 kg/dm² Mounting rail 3 kg/rail,</i>
<i>Totally insulated</i>	
<i>Suitable for indoor and outdoor installations</i>	
<i>UV resistant</i>	
<i>Halogen free compliance (DIN/VDE 0472, part 815)</i>	
<i>Nominal voltage up to 1000 V AC and 1500 V DC</i>	

*The products conforms to the standards:
EN 62208*

The products fulfils the essential safety requirements for CE conformity marking according to the Low voltage Directive (2014/35/EU).

Product warranty:

Fibox warrants that the products are free from defects in material and workmanship and that they stay functional for a minimum period of 5 years under normal use and service when the notes above are taken account. Product warranty does not cover cable and wire inlets and/or other openings and modifications made to a standard product. Painted cabinets have a three year warranty on the paint finish.



*Allan Schultz Jensen
Director, Product Management*