

CERTIFICATE FI/41581

Our Ref. HEL-CERT221201988-01



Product Range of boxes
Type PICCOLO
Certificate Holder Fibox Oy Ab
HTC Center
Keilaranta 19
FI-02150, Espoo, Finland

Technical information Degree of protection (EN 60529) IP66/IP67
Mechanical strength (EN 62262) IK08 +35/-25 °C
Static loads Mounting plate 1 kg/dm²

Other information Material: Polycarbonate
Empty enclosure
See page 2 for the types

The product is certified according to the following standard(s) EN 62208:2011

Validity This certificate is valid until 2028-01-02 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.

Date of issue 2023-01-02

SGS Fimko Ltd

Signature


Joonas Leinonen
Certification Manager



Manufacturer Fibox Oy Ab
 HTC Center
 Keilaranta 19
 FI-02150, Espoo, Finland

Manufacturing site FiboxPAM Oy
 Rajasilta 6
 FI-33880, Lempäälä, Finland

Directive information The certified product(s) fulfils requirements of mentioned standard(s) which are harmonised under the Low Voltage Directive (2014/35/EU) at the date of issue of the certificate.

Additional information The serie includes the following types:

Type	Size (mm)
Piccolo PC B 65 G/T	110 x 80 x 65
Piccolo PC B 85 G/T	110 x 80 x 85
Piccolo PC C 65 G/T	140 x 80 x 65
Piccolo PC C 85 G/T	140 x 80 x 85
Piccolo PC D 65 G/T	170 x 80 x 65
Piccolo PC D 85 G/T	170 x 80 x 85
Piccolo PC F 65 G/T	230 x 80 x 65
Piccolo PC F 85 G/T	230 x 80 x 85
Piccolo PC H 95 G/T	170 x 140 x 85
Piccolo PC M 95 G/T	230 x 140 x 95
Piccolo PC MH 125 G/T	230 x 140 x 125

Material: Polycarbonate (PC)
Base: f1 tested PC with glass fibre
Cover: f1 tested PC
f1: Suitable for outdoor use with respect to exposure to ultraviolet light and immersion in water in accordance with UL 746C.

Based on: HELES2211001244-1