



TYPE	A	B	C	D
TM 0812	94.0	71.0	81.5	58.0
TM 0816	134.0	71.0	121.5	58.0
TM 1216	134.0	111.0	120.0	90.4
TM 1220	174.0	111.0	160.7	90.4
TM 1224	214.0	111.0	202.5	98.6
TM 1520	174.0	141.0	160.0	118.0