



TYPE	A	B	C	R
TRM 0507	37.0±0.5	48.0±1.0	4.5	2.25
TRM 0808	57.0±0.5	68.0±1.0	4.5	2.25
TRM 0812	95.0±0.5	106.0±1.0	4.5	2.25
TRM 0816	135.0±0.5	146.0±1.0	4.5	2.25
TRM 1212	99.0±0.5	110.0±1.0	4.5	2.25
ARM 0606	37.0±0.5	48.0±1.0	4.5	2.25
ARM 0610	77.0±0.5	88.0±1.0	4.5	2.25
ARM 0615	129.0±0.5	140.0±1.0	4.5	2.25
ARM 0808	54.0±0.5	65.0±1.0	4.5	2.25
ARM 0813	104.0±0.5	115.0±1.0	4.5	2.25
ARM 0818	154.0±0.5	165.0±1.0	4.5	2.25
ARM 0825	229.0±0.5	240.0±1.0	4.5	2.25
PRM 0808	58.0±0.5	69.0±1.0	4.5	2.25
PRM 0811	88.0±0.5	99.0±1.0	4.5	2.25
PRM 0816	138.0±0.5	149.0±1.0	4.5	2.25
PRM 0819	168.0±0.5	179.0±1.0	4.5	2.25